APPROX WEIGHT: 26.56 lbs. STATIONARY LEGS REPLACEMENT - AHA-STLO-RF *** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON 3 1/4" **HOLE CHART*** A = HOLES IN BASE ARE (4) \emptyset 9/16 - (BASE HARDWARE NOT INCLUDED) B = HOLES FOR AHS-8/AHA-6 ARE (4) ϕ 9/16--- 28-154-049 C = HOLES FOR AHS-6 ARE (4) ϕ 1/2----- 28-154-050 MOUNTING HARWARE KIT NEEDED D = HOLES FOR **AHA-2/-4** ARE (4) ϕ 7/16---- 28-154-051 FOR GANTRY MODEL LISTED E = HOLES FOR AHS-2/-4 ARE (4) \emptyset 3/8---- 28-154-052 * = THE AHA-STLO-RF STATIONARY LEG HAS 6 1 HOLES FOR ALL MODELS OF GANTRY CRANES, USE THE HOLES LISTED FOR THE MODEL OF CRANE BEING USED. HOLES IN BASE ARE 9/16 AND SPACED 6 1/2" APART AS SHOWN 3/8" 3-D VIEW **FOR RFFFRFNCF** (4) WELDMENTS AND (4) MOUNTING HARDWARE KITS ARE REQUIRED FOR THE BOLT DOWN OPTION FOR A GANTRY CRANE. 10" DIMENSION TOLERANCE ± 1/4" I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE Ρ 3/8"-Ρ AND LOCAL REGULATIONS AND STANDARDS. R ANY MODIFIED UNITS ARE NON-RETURNABLE 0 [] As marked [] As drawn V თგ" (ø9/16" Α Signed: Date: STANDARD FEATURES **Printed Name:** MODEL NUMBER IS AHA-STLO-RF LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING DISTRIBUTOR'S NAME: **OVERALL WIDTH IS 8"** FOR INTERNAL USE ONLY **OVERALL LENGTH IS 8"** PROJECT SIGN OFF VESTIL MANUFACTURING W.O.# **OVERALL HEIGHT IS 10"** DRAWN BY: MTS **SALES** SALES: X DATE: 03/31/2017 STATIONARY LEGS ARE WELDED ENG. STEEL CONSTRUCTION reference: X FILE NAME: SCALE: 1:4 SPECIAL FEATURES FAB. QUOTED LEAD TIME: Y 28-007-415-002 QUOTE # NONE **POWER** Χ